



## **NEO.E160/e620 (YOC 2024.04, E01600005)**

- 1600kN clamp force + electric injection unit with screw D42
- Locating ring FP & MP Ø 160mm
- 1x hydr. cores + 2+2x blow valve+ 2x hydr. cascades+ 1 pneum. Cascade +
- 8x hotrunner control circuits + 8x hydr. Cascades + 1x needle valve IU +
- Special wear resistance II for IU
- EM67 + plug 16A + EM73+ servicenet + 5 programmable In-/Outputs
- ORCA 4+4 including hosing to clamping unit, VNC control integration



## **NEO.E260/e1100 (YOC 2024.10, E02600096)**

- 2600kN clamp force + electric injection unit with screw D55
- Locating ring FP&MP (not going through) Ø 160 mm
- 1+1x hydr. cores + 1x pneu. Core + 3x Blow valves
- 12x hotrunner control circuits + 2x hydr. Cascades + 1xpneu. Casades
- RFID + EM67 + plug 32A + E78



## **NEO.E3207E1400h (YOC 2024.10, E03200023)**

- 3200kN clamp force + electric injection unit with screw D60
- Locating ring FP&MP Ø 160 mm
- 1+1x hydr. cores + 1x pneu. Core + 3x Blow valves
- 12x hotrunner control circuits + 2x hydr. Cascades + 1xpneu. casades
- Special wear resistance I for screw + barrel +EM67 + plug 32A



## **NEO.T130/i380 (YOC 2024.09 T01306007))**

- 1300kN clamp force + hydraulic injection unit with screw D42
- Locating ring FP & MP Ø 100 mm
- 2x hydr. cores + 1x pneum. Core + 2+2 x blow valves
- 8x hotrunner control circuits, RFID, Water 2x 6 fold (FWAP, BWAP) hoses to bulk plates, dosing signal
- Dosing signal
- EM67 + Plug 32A



## **NEO.T90/i380 (YOC 2024.07, T00906029)**

- 900kN clamp force + hydraulic injection unit with screw D35 (with insulation)
- Locating ring FP+ MP Ø 100 mm
- 2x hydr. cores + 2+2x blow valves +6x hotrunner control circuits
- EM67 + 32A plug




## **NEO.H680/i4800 (YOC 2022.03, H0680015)**

- 6800kN clamp force + electric injection unit with screw D90
- Locating ring FP Ø 125 mm, MP none
- 2x2 hydr. cores + 1 pneum. Core
- 32x hotrunner control circuits + 8x hydr. cascades
- EM67
- Special wear resistance I for screw + barrel



## **NEO.E478c/e2300 (YOC 2022.03, E04780033)**

- 4780kN clamp force + electric injection unit with screw D70
- Locating ring FP & MP Ø 200 mm MP Ø 100 mm
- 2x2 hydr. cores + 1 pneum. core
- 32x hotrunner control circuits + 8x hydr. cascades
- EM67
- Special wear resistance I for screw + barrel



## **Robot Yaskawa GP 12 (YOC 2022.07, YR-1-06VXH12-A00)**

- Robot cell in PVM Laboratory, Munich
- Incl. robot console
- Incl. safety fence
- Incl. conveyor belt

# MORETTO LAB EQUIPMENT – PVM – KUTENO 2025

\*



| Odoo    | Bezeichnung                                                                 | Menge |
|---------|-----------------------------------------------------------------------------|-------|
| 990.085 | GRANULAT Fördergerät Moretto 50 kg/h (YOC 2021)                             | 1     |
| 990.086 | GRANULAT Fördergerät Moretto 80 kg/h (YOC 2021)                             | 1     |
| 990.089 | Aufsatztrockner ohne Druckluft Moretto X COMB XD15 48Ltr. XD15 A (YOC 2021) | 1     |
| 990.082 | MOBILES KÜHLGERÄT Moretto RC6 A 6,8 KW (YOC 2021)                           | 1     |
| 990.081 | Temperiergerät Moretto TE-KO Sky 6kW (YOC 2021)                             | 4     |
| 990.030 | Temperiergerät Moretto TE-KO Sky 9kW (YOC 2021)                             | 3     |
| 990.084 | EDELSTAHL-LAGERBEHÄLTER AUF ROLLEN 120 LTR. Moretto CS0 (YOC 2021)          | 2     |
| 990.085 | EDELSTAHL-LAGERBEHÄLTER AUF ROLLEN 240 LTR. Moretto CS1 (YOC 2021)          | 2     |